

## CHERRY STREAM KEYBOARD



Models may vary from the image shown

CHERRY stands for the highest standards of reliability, durability and an incomparable typing feel. The CHERRY STREAM KEYBOARD improves what millions of satisfied users already appreciated in its predecessor. The classic has been updated for a new age.

Especially in the office environment, input devices are our daily companions and are in use for hours. The STREAM KEYBOARD sets new standards in this area and has the potential to become the most popular keyboard.

The mixture of conventional design, a pinch of elegance and simple purism make the keyboard the ideal companion in the office and at home that can suit many tastes. Thanks to the integrated metal plate, the STREAM KEYBOARD will impress users with its ideal torsional stiffness and stability despite its slim design. The two feet and eight rubber pads on the underside also ensure a firm stand when folded in and out.

CHERRY scissor technology has always been associated with an incomparable typing feel and uncompromising precision. During development, special attention was paid to noise created by typing. The noise development has been further reduced in comparison with the very quiet predecessor model. This makes the keyboard the first choice for offices with many workplaces or if you like to type quietly.

Our careful selection of materials ensures that the letters stand out clearly from the keys and that you can work in a fatigue-free manner.

The status LEDs for CAPS LOCK, NUM and SCROLL LOCK integrated directly into the key are a unique feature that is otherwise only found in much higher price ranges. The red status LEDs show you at first glance whether the caps lock key has been pressed.

Ten additional practical keys make work in Microsoft Office and multimedia applications easier. It includes six commonly used keys for controlling your multimedia player. In addition, the browser, email, and calculator functions give you easy access to frequently used commands at all times. A lock button allows users to log out at the push of a button before leaving their workstation. This is particularly invaluable in the office environment.

Despite these additional keys, no separate drivers are required. The STREAM KEYBOARD is a plug&play device.

In working environments, in particular, compliance with guidelines, quality and environmental goals is obligatory. For CHERRY, these goals are also part of its corporate philosophy. This is why we have put our efforts into our successful bid to gain the "Blauer Engel" award. In addition, the GS "Safety Tested" seal certifies that the product complies with all relevant European directives and regulations relating to health protection.

Are you looking for a reliable companion who will not let you down in your daily work or your private life? The CHERRY STREAM KEYBOARD is the perfect choice.

### Function & performance

**Maximum productivity:** Extremely quiet keystrokes, unbeatable typing feel

**Highest quality:** Durable, abrasion resistant, our own SX scissor mechanism, "Blauer Engel" eco-label

**Optimum operating comfort:** 3 integrated status displays, perfect slip resistance, 10 Office & multimedia keys

**Very latest design:** Flat overall height, focused on the essentials, GS approval

# CHERRY STREAM KEYBOARD

## Technical Data

### Layout (country or language):

Product dependant, see table "Models"

### Housing colour:

Product dependant, see table "Models"

### Key colour:

Product dependant, see table "Models"

### Weight (product):

approx. 910 g

### Total weight (with packaging):

approx. 1100 g

### Cable Length:

approx. 180 cm

### Storage Temperature:

-20 °C to 60 °C

### Operating Temperature:

0 °C to 40 °C

### Current Consumption:

typ. 20 mA

### Interface:

USB

### Product approvals:

- cURus
- VDE-GS
- CE
- FCC



### Dimensions (product):

approx. 463 x 163 x 18 mm (with feet up: 29,5 mm)

### Packaging dimensions:

approx. 480 x 210 x 24 mm

### Keyboard:

- Degree of protection: Spill resistant
- Service life, standard key: > 20 million key operations
- Number of Keys: Product dependant, see table "Models"
- Number of Hotkeys: 10
- Function Hotkey: Volume down, Sound on/off, Volume up, Previous title, Next title, Play/pause, Blocking the PC, Browser, E-Mail program, Calculator

### System requirements:

USB connection

### Delivery Volume

- CHERRY STREAM KEYBOARD
- Operating instructions

### Packaging Unit:

Number of products in the master package: 10

Number of master packages per pallet: 36

### Warranty:

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below.

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

#### Conditions for the extended warranty

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

## CHERRY STREAM KEYBOARD

### Models:

Possible country/layout versions

Product name	Order number	Layout (country or language)	Housing colour	Key colour	Number of Keys	EAN code
CHERRY STREAM KEYBOARD	JK-8500BE-0	Belgium	pale grey	pale grey	105 + 10	4025112090301
CHERRY STREAM KEYBOARD	JK-8500BE-2	Belgium	black	black	105 + 10	4025112090318
CHERRY STREAM KEYBOARD	JK-8500CH-0 *	Switzerland	pale grey	pale grey	105 + 10	4025112090240
CHERRY STREAM KEYBOARD	JK-8500CH-2	Switzerland	black	black	105 + 10	4025112090257
CHERRY STREAM KEYBOARD	JK-8500CS-0 *	Czech Republic / Slovakia	pale grey	pale grey	105 + 10	4025112091339
CHERRY STREAM KEYBOARD	JK-8500CS-2 *	Czech Republic / Slovakia	black	black	105 + 10	4025112091346
CHERRY STREAM KEYBOARD	JK-8500DE-0	Germany	pale grey	pale grey	105 + 10	4025112090165
CHERRY STREAM KEYBOARD	JK-8500DE-2	Germany	black	black	105 + 10	4025112090172
CHERRY STREAM KEYBOARD	JK-8500ES-0 *	Spain	pale grey	pale grey	105 + 10	4025112090356
CHERRY STREAM KEYBOARD	JK-8500ES-2 *	Spain	black	black	105 + 10	4025112090363
CHERRY STREAM KEYBOARD	JK-8500EU-0	US English with EURO symbol	pale grey	pale grey	104 + 10	4025112090226
CHERRY STREAM KEYBOARD	JK-8500EU-2	US English with EURO symbol	black	black	104 + 10	4025112090233
CHERRY STREAM KEYBOARD	JK-8500FR-0	France	pale grey	pale grey	105 + 10	4025112090189
CHERRY STREAM KEYBOARD	JK-8500FR-2	France	black	black	105 + 10	4025112090196
CHERRY STREAM KEYBOARD	JK-8500GB-0	UK	pale grey	pale grey	105 + 10	4025112090202
CHERRY STREAM KEYBOARD	JK-8500GB-2	UK	black	black	105 + 10	4025112090219
CHERRY STREAM KEYBOARD	JK-8500IT-0 *	Italy	pale grey	pale grey	105 + 10	4025112090288
CHERRY STREAM KEYBOARD	JK-8500IT-2 *	Italy	black	black	105 + 10	4025112090295
CHERRY STREAM KEYBOARD	JK-8500PN-0 *	Pan-Nordic	pale grey	pale grey	105 + 10	4025112090264
CHERRY STREAM KEYBOARD	JK-8500PN-2 *	Pan-Nordic	black	Black	105 + 10	4025112090271

\* On request