



# Classic filament LED candles and lustres

## Classic LEDLuster ND 2-25W P45 B22 827 CL

Featuring a classic heritage design, filament LED candles and lustres combine the familiar shapes of classic incandescent candles or lustres with the benefits of long-lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lustres.

### Product data

General Information	
Cap base	B22 [ B22]
EU RoHS compliant	Yes
Nominal lifetime (nom.)	15000 h
Switching cycle	20,000X
Technical type	2-25W
Light Technical	
Colour code	827 [ CCT of 2,700 K]
Luminous flux (nom.)	250 lm
Colour designation	Warm white (WW)
Correlated Colour Temperature (Nom)	2700 K
Luminous efficacy (rated) (nom.)	125.00 lm/W
Colour consistency	<6
Color rendering index (nom.)	80
LLMF at end of nominal lifetime (nom.)	70 %
Operating and Electrical	
Input frequency	50 to 60 Hz
Power (Rated) (Nom)	2 W

Lamp current (nom.)	20 mA
Wattage equivalent	25 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light (nom.)	0.5 s
Power factor (nom.)	0.4
Voltage (Nom)	220-240 V
Temperature	
T-Case maximum (nom.)	30 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb finish	Clear
Approval and Application	
Energy efficiency label (EEL)	A++
Energy Consumption kWh/1000 h	2 kWh


# Classic filament LED candles and lustres

## Product Data

Full product code	871869676696500
Order product name	Classic LEDLuster ND 2-25W P45 B22 827 CL
EAN/UPC – product	8718696766965
Order code	76696500
Numerator – quantity per pack	1

Numerator – packs per outer box	10
Material no. (12NC)	929001815902
Net weight (piece)	0.010 kg


## Dimensional drawing




Bulb P45 230V 2-25W 250lm 2700K B22 ND

Product	D	C
Classic LEDLuster ND 2-25W P45 B22 827 CL	45 mm	78 mm


## Photometric data



CLA LEDlustre 25W B22 827 CL P45




LEDbulb 40W B22 827 CL A60 ND




CLA LEDcandle 25W B15 827 CL B35

## Classic filament LED candles and lustres

### Lifetime



LEDbulb 60W E14 827 FR B38



LEDbulb 60W E14 827 FR B38

