



PRODUCT-DETAILS

TY125-18-100

CBL TIE 18LB 5IN NATURAL NYLON



General Information

Extended Product Type	TY125-18-100
Product ID	7TCG054360R0106
EAN	5414363060420
Catalog Description	CBL TIE 18LB 5IN NATURAL NYLON
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 142mm (5.59 Inches), Width of 2.5mm (0.10 Inches), Thickness of 1.2mm (0.05 Inches), Tensile Strength Rating of 80 Newtons (18 Pounds), 100 Pack

Ordering

EAN	5414363060420
Customs Tariff Number	3926909990

Dimensions

Product Net Weight	.001 lb .454 g
--------------------	-------------------

Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	1 in 25 mm

Package Level 1 Height	6 in 152 mm
Package Level 1 Depth / Length	10 in 254 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	6.9 in 175 mm
Package Level 2 Height	6.5 in 165 mm
Package Level 2 Depth / Length	8.5 in 216 mm

Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	1.25 in 31.75 mm
Color	Natural
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	NYLON CABLE TIE
Product Type	General Purpose
Tensile Strength	18 lb 80 N
Thickness	0.05 in 1.2 mm
UPC	786210288130

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY125-18-100
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY125-18-100

Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

