

acer



PROJECT THE FUTURE OF BUSINESS MEETINGS



Acer P1555

Full HD (1920 x 1080) resolution

4,000¹ ANSI lumens

Acer LumiSense content-aware

Digital lens shift

Up to 20,000-hour lamp life (EcoPro)



BluelightShield™



LUMISENSE



ColorSafe II



ColorBoost 3D

Expressive display

- Full HD (1920 x 1080) resolution
- 4,000 ANSI lumens
- 10,000:1 contrast ratio
- Acer LumiSense
- Acer ColorBoost3D
- Acer ColorSafe II
- Acer BlueLightShield
- HDMI 3D

Enhanced usability

- 1080p 120Hz
- Low input lag 8.3ms
- Wireless Projection²
- 10W built-in speaker
- Acer Display Widget

Installation flexibility

- Digital Lens Shift (vertical)
- Image Shift
- 1.2X zoom
- Auto Keystone Correction +/- 40°
- Auto ceiling-mounted correction
- AC power on
- 24/7 operation

Eco-friendly functionality

- Lamp life up to 20,000 hours (EcoPro)

1 - The brightness is measured under WUXGA resolution.

2 - Wireless dongle (optional accessory) is required for wireless projection.

Model name	P1555
Projection system	DLP®
Resolution	1080p (1,920 x 1,080) Maximum WUXGA (1,920 x 1,200)
Brightness	4,000 ¹ ANSI Lumens (Standard), 3,200 ANSI Lumens (ECO) (Compliant with ISO 21118 standard)
Aspect ratio	16:9 (Native), 4:3 (Supported)
Contrast ratio	10,000:1
Throw ratio	1.47 ~ 1.76 (61"@2m)
Zoom ratio	1.2X
Projection lens	F = 1.94 ~ 2.06, f = 15.57mm ~ 18.67mm, Manual Zoom & Focus
Digital Lens Shift	0% ~ 11% (Vertical shift)
Lamp life	4,000 Hours (Standard), 10,000 Hours (ECO), 20,000 Hours (EcoPro)
Noise level	30 dBA (Standard), 26 dBA (ECO), 27 dBA (EcoPro)
Input interface	Analog RGB/Component Video (D-sub) x 2 Composite Video (RCA) x 1 HDMI (Video, Audio, HDCP) x 1 HDMI/MHL (Video, Audio, HDCP) x 1 PC Audio (Stereo mini jack) x 1
Output interface	Analog RGB (D-sub) x 1 PC Audio (Stereo mini jack) x 1 DC Out (5V/1.5A, USB Type A) x 1
Control interface	USB (Type A) x 1, share output port RS232 (D-sub) x 1
Dimensions	322 x 225 x 91 mm (12.7" x 8.9" x 3.6")
Weight	2.9 Kg (6.4 lbs)

Product View

