



Product Data Sheet

www.brannan.co.uk

Stainless Steel Water Resistant Test Thermometer

Robust, water resistant thermometer (to IP65) with hold function and auto power off. Thermometer has hanging hook and 125mm stainless steel (304) probe with pocket case and clip.

Probe thermometers can be supplied with UKAS Calibration Certificate or Statement of Conformity on request.

Supplied in individual box with full instructions.

Product Specifications

- Temperature Range:** -40 to +200°C
- Accuracy:**
 - 40 to -1°C: +/-2°C
 - 0 to 100°C: +/-1°C
 - 101 to 150°C: +/-2°C
 - 151 to 200°C: +/-5°C
- Resolution:** 0.1°C
- Ingress Protection:** IP65
- Battery:** LR44 x 1 pc (included)
- Auto-Off:** After 10 minutes of inactivity
- CE:** Approved
- ROHS/WEEE:** Compliant
- Hazard Information (SDS):** See www.brannan.co.uk for information
- LCD Dimensions:** 11mm x 30mm
- Probe Length:** 120mm
- Probe Diameter:** 3.5mm ø
- Product Dimensions:** 190mm x 25mm x 12mm
(Length = 229mm when in pocket case)
- Product Weight:** Net - 59g
- Packaged Dimensions:** 230mm x 27mm x 24mm



Description	Barcode	Product No
Stainless Steel Water Resistant Test Thermometer	5 011405 311658	31/165/0