

## Product Specifications

### SRH1440 Professional Open Back Headphones

#### Overview

Designed for mastering and critical listening, SRH1440 Professional Open Back Headphones from Shure provide full range audio with detailed highs and rich bass in a sleek, attractive design. The premium-padded headband with steel frame provides hours of listening comfort. An included storage case, replacement set of velour earpads, and an additional cable ensures years of uninterrupted listening enjoyment.

#### Features

- 40 mm neodymium drivers deliver full-range audio with rich, controlled bass
- Open-back, circumaural design for exceptionally natural sound, wide stereo image, and increased depth of field
- Impedance optimized for direct connection to wide range of portable audio devices
- Fully adjustable, premium padded headband with steel frame and sleek, ergonomic design for hours of listening comfort
- Oxygen-free copper cable (OFC) with Kevlar® reinforced jacket for superior performance and durability
- Dual-exit cables with gold-plated MMCX connectors provide secure connection and detachability for easy storage or replacement
- Replaceable velour ear pads with high density, slow recovery foam for exceptional comfort
- Additional oxygen-free copper cable and zippered storage case provide years of listening enjoyment and convenient storage
- Individually tested and serialized
- Legendary Shure durability to withstand the rigors of everyday use

#### Available Models

SRH1440	Includes a threaded 1/4" gold-plated adapter, zippered storage case, (2) dual-exit detachable cables, and additional pair of velour ear pads
---------	--

#### Specifications

Transducer Type	Dynamic, Neodymium magnet
Driver Size	40 mm
Frequency Range	15 Hz - 27,000 Hz
Sensitivity (@ 1 kHz)	101 dB/mW
Impedance (@ 1 kHz)	37 Ohms
Maximum Input Power	1000 mW
Connector	Gold-plated 3.5 mm (1/8") stereo mini jack plug with 6.35 mm (1/4") threaded adapter
Cable Length/Type	6.9 ft (2.1 m) dual-exit, detachable oxygen-free copper
Removable Ear Pads	Yes
Collapsible	No
Weight (without cable)	.76 lb (343 g)

#### Accessories and Replacement Parts

Replacement Velour Ear Pads	HPAEC1440
Locking 1/4" Adapter	HPAQ1
Zippered, Hard Storage Case	HPACC2
Replacement Dual-Exit Detachable Cable	HPASCA2

