

## Product Specifications

### SRH240A Professional Quality Headphones

#### Overview

The SRH240A Headphones provide excellent sound reproduction and comfort. With 40 mm neodymium dynamic drivers optimized for general listening and monitoring, the SRH240A Headphones reproduce full bass with clear mids and highs. Impedance, power handling and sensitivity are all calibrated for connection to most consumer and professional audio devices.



#### Features

- Wide frequency range delivers full bass and detailed highs
- New re-engineered headband and earcup construction for a more ergonomic, comfortable fit
- Optimized performance for use with most pro and consumer audio devices
- Closed-back, circumaural design rests comfortably over the ears and reduces background noise
- Legendary Shure quality to withstand the rigors of everyday use
- Replaceable ear pads ensure long product life

#### Available Models

SRH240A	Includes a threaded ¼" nickel plated adapter
---------	--

#### Specifications

Transducer Type	Dynamic, Neodymium magnet
Driver Size	40 mm
Frequency Range	20 Hz - 20,000 Hz
Sensitivity (@ 1 kHz)	107 dB/mW
Impedance (@ 1 kHz)	38 Ohms
Maximum Input Power	500 mW
Connector	Gold-plated 3.5 mm (1/8") stereo mini jack with 6.35 mm (1/4") threaded adapter
Cable Length/Type	2 meters (6.56 ft) / attached, straight, oxygen-free copper
Removable Ear Pads	Yes
Weight	.52 lb (238 g) without cable

#### Accessories and Replacement Parts

Replacement Ear Pads	HPAEC240
Locking 1/4 Adapter	HPAQA1
Carrying Pouch	HPACP1