

Product Specifications

SRH440 Professional Studio Headphones

Overview

The SRH440 Professional Studio Headphones provide exceptional sound reproduction and comfort. Optimized for home and studio recording, SRH440 headphones reproduce accurate audio across an extended range. Impedance, power handling and sensitivity are all calibrated for professional audio devices such as DJ mixers, mixing consoles, and headphone amplifiers.



Features

- Enhanced frequency response delivers accurate audio across an extended range
- Closed-back, circumaural design rests comfortably over the ears and reduces background noise
- Impedance and power handling optimized for performance with professional audio devices
- Adjustable headband and collapsible construction provide comfort and portability
- Legendary Shure quality to withstand the rigors of everyday use
- Bayonet clip securely locks cable into ear cup
- Replaceable ear cup pads ensure long product life
- 3 meter coiled, detachable cable provides plenty of length and easy storage and replacement

Available Models

SRH440	Includes a threaded ¼" gold plated adapter and carrying bag
--------	---

Specifications

Transducer Type	Dynamic, Neodymium magnet
Driver Size	40 mm
Frequency Range	10 - 22,000 Hz
Sensitivity (@ 1 kHz)	105 dB/mW
Impedance (@ 1 kHz)	44 Ohms
Maximum Input Power	500 mW
Connector	Gold-plated 3.5 mm (1/8") stereo mini jack plug with 6.35 mm (1/4") threaded adapter
Cable Length/Type	3 meters (9.84 ft) / detachable coiled, oxygen-free copper
Removable Ear Pads	Yes
Collapsible	Yes
Weight	.69 lb (311 g) without cable

Accessories and Replacement Parts

Replacement Ear Pads	HPAEC440
Locking 1/4 Adapter	HPAQA1
Carrying Pouch	HPACP1
Replacement Cable Assembly	HPACA1