



PRO LINEAR LOWBAYS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 892 - 934 938

[View more details](#)

TECHNICAL INFORMATION

Watts:	100
Lumens:	12000
Input Power:	AC:220-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	Black
Body Type:	Aluminium
PF:	0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	80
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	120°
Color:	6500K
Dimension:	537x130x96mm
lumens per watt:	120
LED Chip Solution:	18V 60mA



FEATURES

- Powerful LED light source with lumen efficiency of 120 LM/W
- Fitted with high efficiency Samsung LED Chips that offer up to 80% in energy savings
- Excellent glare index for low mounting operations
- Longevity and efficient lumen maintenance
- Suitable for industrial usage, warehouses, supermarkets, workshops, factories, warehouses, highways, toll stations, gas stations, malls, exhibition halls, and stadiums
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

PACKAGING

Gross Weight (Kgs): **2.777**
Unit CBM: **0.0078975**
Dimension: **537x130x96mm**

MASTER BOX PACKAGING

Box Qty: **9**
Qty Per Pallet: **126**
Length (Box) mm: **100**
Width (Box) mm: **585**
Height (Box) mm: **135**

LISTING DETAILS

Commodity Code: **9405403990**
EanCode: **3800157646109**

CE/EMC

CE/LVD

