



### TECHNICAL INFORMATION

Watts:	200
Lumens:	24000
Input Power:	AC:220-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	Black
Body Type:	Aluminium
PF:	>0.9
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	120°
Color:	4000K
Dimension:	1059x130x96mm
lumens per watt:	120
LED Chip Solution:	18V 60mA

### PRO LINEAR LOWBAYS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 895 - 936 938

[View more details](#)



### FEATURES

- Powerful LED light source with lumen efficiency of 120 LM/W
- Fitted with high efficiency Samsung LED Chips that offer up to 80% in energy savings
- Excellent glare index for low mounting operations
- Longevity and efficient lumen maintenance
- Suitable for industrial usage, warehouses, supermarkets, workshops, factories, warehouses, highways, toll stations, gas stations, malls, exhibition halls, and stadiums
- Recommended daily usage: 10 - 12 hours \*Exceeding recommended daily usage will void warranty

### PACKAGING

Gross Weight (Kgs): 4.6  
Unit CBM: 0.014985  
Dimension: 1059x130x96mm

### MASTER BOX PACKAGING

Box Qty: 6  
Qty Per Pallet: 54  
Length (Box) mm: 100  
Width (Box) mm: 1110  
Height (Box) mm: 135

### LISTING DETAILS

Commodity Code: 9405403990  
EanCode: 3800157646130

CE/EMC

CE/LVD

