



F SERIES

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 6184 - 1415 940

[View more details](#)

TECHNICAL INFORMATION

Watts:	48
Lumens:	3840
Shape:	Rectangle
Input Power:	AC:200-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	PC + ABS
PF:	>0.7
LED Chip Type:	SMD
CRI:	>70
Operation Temperature:	-20°C to +40°C
Dimmable:	No
Beam Angle:	120°
Color:	4500K
Dimension:	1500x76x66mm
Output Voltage:	DC:80-110V



IP65
RATING



2 YEAR
WARRANTY



IK 05



SAVE UP TO
80%
ENERGY

FEATURES

- Using high power SMD technology which makes it more reliable and durable
- Complete protection from water, dust and corrosion - IP65 Rated
- Designed for maximum efficiency & minimal glare
- Save up to 80% in electricity consumption compared to a fluorescent lighting fixture
- Long Lifespan, Low maintenance and energy saving
- Excellent heat dissipation
- Suitable for parking lots, warehouses, garages, storage docks, workshops etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warrant

CE/EMC

CE/LVD



SMD LED'S

80% energy savings through modern LED technology



PACKAGING

Gross Weight (Kgs): 1.805
Unit CBM: 0.00992
Dimension: 1500x76x66mm

MASTER BOX PACKAGING

Box Qty: 12
Qty Per Pallet: 120
Length (Box) mm: 1550
Width (Box) mm: 80
Height (Box) mm: 80

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157602389