



F SERIES

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 6201 - 1406 940

[View more details](#)

TECHNICAL INFORMATION

| | |
|------------------------|----------------------|
| Watts: | 36 |
| Lumens: | 2880 |
| Shape: | Rectangle |
| Input Power: | AC:200-240V, 50/60Hz |
| Long Life: | 20,000 Hours |
| Unit Color: | White |
| Body Type: | PC + ABS |
| PF: | >0.9 |
| LED Chip Type: | SMD |
| CRI: | >70 |
| Operation Temperature: | -20°C to +40°C |
| Dimmable: | No |
| Beam Angle: | 120° |
| Color: | 6000K |
| Dimension: | 1200x76x66mm |

SMD LED'S

80% energy savings through modern LED technology

4
FEET



FEATURES

- Using high power SMD technology which makes it more reliable and durable
- Complete protection from water, dust and corrosion - IP65 Rated
- Designed for maximum efficiency & minimal glare
- Save up to 80% in electricity consumption compared to a fluorescent lighting fixture
- Long Lifespan, Low maintenance and energy saving
- Excellent heat dissipation
- Suitable for parking lots, warehouses, garages, storage docks, workshops etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warrant

PACKAGING

Gross Weight (Kgs): 1.45
Unit CBM: 0.00713124
Dimension: 1200x76x66mm

MASTER BOX PACKAGING

Box Qty: 12
Qty Per Pallet: 180
Length (Box) mm: 1250
Width (Box) mm: 80
Height (Box) mm: 80

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157603287

CE/EMC

CE/LVD

