



TECHNICAL INFORMATION

Input Power:	AC:220-240V, 50Hz
Unit Color:	Silver
Body Type:	Stainless Steel
Operation Temperature:	-25°C to +50°C
Rated Load:	Max 35W
Dimension:	60x60x420mm

GARDEN SPIKES FITTINGS

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 7518 - 1246

[View more details](#)



FEATURES

- Garden spike fitting designed for easy installation
- Strong and sturdy Stainless Steel body
- Ingress protection IP44
- Compatible with GU10 holder type (Fitting only - light not included)
- Easy to install and requires little maintenance
- Suitable for pathways, driveways, tree uplighting etc.

CE/EMC CE/LVD



PACKAGING

Gross Weight (Kgs): 0.56
Unit CBM: 0.002275
Dimension: 60x60x420mm

MASTER BOX PACKAGING

Box Qty: 8
Qty Per Pallet: 576
Length (Box) mm: 125
Width (Box) mm: 70
Height (Box) mm: 260

LISTING DETAILS

Commodity Code: 9405109890
EanCode: 3800157617772