



TECHNICAL INFORMATION

Input Power:	AC/DC:12V
Unit Color:	Black+Silver
Body Type:	Stainless Steel
Dimmable:	No
Rated Load:	Max 20W
Dimension:	Ø87x128mm
Type:	One Window

UNDERGROUND FITTINGS MR16

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 8567 - 2689

[View more details](#)

UNDERGROUND FITTINGS

AC/DC 12V

MR16

Compatible with any standard MR16 lamp.

*Lamps are not included



IP67
RATING



3 YEAR
WARRANTY

FEATURES

- Perfect replacement for traditional underground fittings
- Strong and sturdy Stainless Steel body
- Ingress protection IP67
- Easy to install and requires little maintenance
- Compatible with MR16 holder type (Fitting only - light not included)
- Suitable for pathways, driveways, tree uplighting etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty



PACKAGING

Gross Weight (Kgs): 0.766
Unit CBM: 0.0015
Dimension: Ø87x128mm

MASTER BOX PACKAGING

Box Qty: 12
Qty Per Pallet: 600
Length (Box) mm: 100
Width (Box) mm: 100
Height (Box) mm: 150

LISTING DETAILS

Commodity Code: 9405109890
EanCode: 3800157644518