



TECHNICAL INFORMATION

Watts:	5
Lumens:	800
Input Power:	AC:100-240V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	ABS + Aluminium
LED Chip Type:	SMD
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	Yes
Color:	3IN1
Dimension:	440x120x40mm
Input Current :	5V, 3A
No. Of Led:	54

WIRELESS CHARGING LAMPS | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 8603 - 1263 940

[View more details](#)



SLEEK & ELEGANT DESIGN WITH
ABS &
ALUMINUM DESIGN



IP20
RATING



2 YEAR
WARRANTY



80%
ENERGY
SAVING



CRI>80

FEATURES

- Sleek and elegantly designed table lamp with wireless charging built-in
- Adjustable brightness with 3 levels of dimming
- LUX output - 800LUX
- Wireless Charging Output: 5W (5V, 1A)
- USB Output 5V, 0.5A(2.5W)
- Time to reach the brightest 2s
- Built-in Eye protection feature
- Included: 18W fast charging adapter (3A)
- Suitable for bedrooms, living rooms, offices etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty



PACKAGING

Gross Weight: 0.618
Unit CBM: 0.0027495
Dimension: 440x120x40mm

MASTER BOX PACKAGING

Box Qty: 10
Qty Per Pallet: 400
Length (Box) mm: 130
Width (Box) mm: 470
Height (Box) mm: 45

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157650564