



### TECHNICAL INFORMATION

Watts:	3.2
Lumens:	385
Shape:	T16
Input Power:	12V AC/DC
Long Life:	30,000 Hours
Body Type:	Plastic Clad Aluminium
PF:	>0.4
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-25°C to +50°C
Dimmable:	No
Beam Angle:	300°
Color:	3000K
Equivalence Watts:	30
Dimension:	16x46.5mm

### G4 CAPSULES PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 131 - 1241 2938

[View more details](#)

### LED CAPSULES LIGHT



### G4 LED Spotlights

A+ ENERGY RATING

85% ENERGY SAVING

provided by  
**SAMSUNG**

5 YEAR WARRANTY



### FEATURES

- Stable SMD-Samsung Chip technology for better reliability and longer lifespan
- Lasts hours, longer life span than Standard halogen spotlights
- Replaces old halongen lamp
- Easy to install, designed with G4 base
- Excellent Heat Radiation Efficiency
- Instant start - No Mercury - No UV radiation
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc
- Note: Suitable and Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

CE/EMC



### PACKAGING

Gross Weight (Kgs): 0.015  
Unit CBM: 0.000378  
Dimension: 16x46.5mm

### MASTER BOX PACKAGING

Box Qty: 300  
Qty Per Pallet: 205  
Length (Box) mm: 30  
Width (Box) mm: 90  
Height (Box) mm: 140

### LISTING DETAILS

EanCode: 3800157639385