



TECHNICAL INFORMATION

Watts:	22
Lumens:	3000
Shape:	T8
Input Power:	AC:220-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	Plastic
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Dimmable:	No
Beam Angle:	160°
Color:	6400K
Equivalence Watts:	75
Dimension:	1500x27.9mm
lumens per watt:	120

T8 120 LUMEN PRO TUBES

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 675 - 1405 940

[View more details](#)

T8 NANOPLASTIC LED TUBE



- Better light transmittance and angle – diffuses glare
- Higher durability than PC and glass tubes
- Cost-effective, safe retrofit for T8 tubes

5
FEET

120
LM/WATT





5 YEAR WARRANTY



FEATURES

- Nano-plastic tube offers better light transmittance - Lumen efficiency of 120 LM/W
- Higher endurance and longevity compared to PC and glass
- Cost effective, safe retrofit for T8 Tubes
- Fitted with high efficiency SMD-Samsung Chip LED Chips
- Super thermal conductivity - Constant current integrated IC driver
- Wide light angle effectively diffuses glare
- Suitable for domestic and commercial lighting, offices, supermarkets, shops, hotels and many more
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

PACKAGING

Gross Weight (Kgs): 0.209
Unit CBM: 0.001395
Dimension: 1500x27.9mm

MASTER BOX PACKAGING

Box Qty: 25
Qty Per Pallet: 700
Length (Box) mm: 30
Width (Box) mm: 30
Height (Box) mm: 1550

LISTING DETAILS

EanCode: 3800157632942

CE/EMC

CE/LVD

