



TECHNICAL INFORMATION

Watts:	7
Lumens:	600
Shape:	P45
Input Power:	AC:220-240V, 50Hz
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	Thermoplastic
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	180°
Color:	3000K
Equivalence Watts:	45
Dimension:	Ø45x81mm
LED Chip Solution:	9V 100mA


GOLF E14 PRO | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 863 - 1440 940

[View more details](#)



FEATURES

- Modern LED SMD-Samsung Chip technology for better reliability and durability
- Replaces 45 watts old halogen lamp
- High color rendering index CRI >80
- Lasts hours, longer life span than Standard halogen spotlights
- High luminous efficacy and low power consumption
- Designed for E14 standard holder
- Excellent power factor and integrated IC driver
- Suitable for residential lighting, commercial lighting, decorative, living rooms, lounges etc.
- Recommended daily usage: 10 - 12 hours *Exceeding recommended daily usage will void warranty

PACKAGING

Gross Weight (Kgs): 0.026
Unit CBM: 0.00019125
Dimension: Ø45x81mm

MASTER BOX PACKAGING

Box Qty: 200
Qty Per Pallet: 5600
Length (Box) mm: 45
Width (Box) mm: 50
Height (Box) mm: 85

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157640084

CE/EMC

CE/LVD

