



### TECHNICAL INFORMATION

Watts:	6.5
Lumens:	450
Input Power:	DC:12V
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	Plastic
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	110°
Color:	4000K
Equivalence Watts:	40
Dimension:	50x55mm
LED Chip Solution:	9V 100mA

### MR16 LENS 110° | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

*One brand, endless solutions..*

SKU: 205 - 1250 940

[View more details](#)

### LED SPOTLIGHT



### FEATURES

- Stable SMD-Samsung Chip technology for better reliability and longer lifespan
- Lasts hours, longer life span than Standard halogen spotlights
- Replaces old halogen lamp
- Easy to install, designed with GU5.3 base
- Excellent Heat Radiation Efficiency
- Instant start - No Mercury - No UV radiation
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc
- Note: Suitable and Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

### PACKAGING

Gross Weight (Kgs): 0.045  
Unit CBM: 0.00015  
Dimension: 50x55mm

### MASTER BOX PACKAGING

Box Qty: 200  
Length (Box) mm: 50  
Width (Box) mm: 50  
Height (Box) mm: 60

### LISTING DETAILS

EanCode: 3800157631709

