



TECHNICAL INFORMATION

Watts:	6.5
Lumens:	450
Input Power:	DC:12V
Long Life:	30,000 Hours
Unit Color:	White
Body Type:	Plastic
PF:	>0.5
LED Chip Type:	SMD-Samsung Chip
CRI:	>80
Operation Temperature:	-20°C to +45°C
Dimmable:	No
Beam Angle:	110°
Color:	6400K
Equivalence Watts:	40
Dimension:	Ø50x49mm
LED Chip Solution:	9V 100mA

MR16 LENS 110° | LED LIGHTING

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.

One brand, endless solutions..

SKU: 206 - 1250 940

[View more details](#)

LED SPOTLIGHT



FEATURES

- Stable SMD-Samsung Chip technology for better reliability and longer lifespan
- Lasts hours, longer life span than Standard halogen spotlights
- Replaces old halongen lamp
- Easy to install, designed with GU5.3 base
- Excellent Heat Radiation Efficiency
- Instant start - No Mercury - No UV radiation
- Applications - Hotels, Bars, Commercial and Residential Lighting and Exhibition Stands etc
- Note: Suitable and Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warrantyy



PACKAGING

Gross Weight (Kgs): 0.045
Unit CBM: 0.00015
Dimension: Ø50x49mm

MASTER BOX PACKAGING

Box Qty: 200
Qty Per Pallet: 7200
Length (Box) mm: 50
Width (Box) mm: 50
Height (Box) mm: 60

LISTING DETAILS

EanCode: 3800157631716