



CRITCHLEY Z-Type Markers



For Cable Diameter mm	For Cable Size mm ² (BS6004) (BS6231)	Marker Size	Marker Length mm	Packed Reel Box	ORDER CODE (Straight Cut)	ORDER CODE (Chevron Cut)
1.5-2.0		5	4.5	1000	0580	1151
2.0-3.2	1.0	7	4.5	1000	0581	1152
2.5-4.0	1.5	9	4.5	1000	0615	1153
2.9-4.7	2.5	11	4.5	1000	0616	1154
3.4-5.7	4.0	13	4.5	1000	0617	1155
3.8-6.3	6.0	15	4.5	1000	0618	1156
4.3-6.9	10.0	18	4.5	500	0620	1157
5.5-8.9	16.0	23	6.0	500	0622	1158
7.9-12.7	25.0	35	6.0	250	0624	1159

Applicators for Z-Type Cable Markers

Size	Z-Type Size	Packed	ORDER CODE
1	7	1	1251
2	9	1	1252
3	11	1	1253
4	13	1	1254
5	15	1	1255
6	18	1	1256

- Gusseted design allows marker to fit firmly over a wide range of cable diameters
- 9 sizes for cables <math><0.5\text{mm}^2</math> to 35mm²
- Clear, legible mark
- Choice of straight or chevron cut
- Colour coded option

Material

PVC

Colour Options

STRAIGHT CUT:

White body marked black:

A-Z, 0-9 and symbols, available on reels or in boxes.

Yellow body marked black:

A-Z, 0-9 and symbols, available on reels only

Colour Coded:

0-9 all sizes, available in boxes.

CHEVRON CUT:

White body marked black:

A-Z, 0-9 and symbols, available in boxes only.

Yellow body marked black:

A-Z, 0-9 and symbols, available on reels only.

Colour Coded:

0-9, size 11 only, available in boxes or on reels.

Service Temperature

-45°C to +70°C

Chemical Resistance

Excellent resistance to sea water, detergents (10% aqueous), fuels, oils, white and industrial spirit.