

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982670249](#)
Status: **Active**
Overview: Premo-Flex Cable Jumpers
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 76.00mm Cable Length, Tin (Sn) Plating, 10 Circuits

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Packaging Specification PK-98267-001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Cable
 Series [98267](#)
 Comments Contacts on the same side, Type A
 Crimp Quality Equipment Yes
 Overview [Premo-Flex Cable Jumpers](#)
 Product Name Premo-Flex FFC Jumper
 UPC 756054770795

Physical

Cable Length 76.00mm
 Circuits (Loaded) 10
 Material - Plating Mating Tin
 Net Weight 0.584/g
 Packaging Type Bag
 Pitch - Mating Interface 1.00mm
 Temperature Range - Operating -40° to +105°C
 Wire Size AWG N/A
 Wire/Cable Type Flat Flex Cable

Electrical

Current - Maximum per Contact 1.2A
 Voltage - Maximum 60V AC

Material Info

Reference - Drawing Numbers

Packaging Specification [PK-98267-001-001](#)
 Sales Drawing [SD-98267-001](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)4578-DC (25
 June 2020)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[98267 Series](#)

Mates With

Easy-On FFC/FPC Connector:

[522071033](#) , [522711079](#) , [526101033](#) ,
[526101034](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION