

## POE-1TR – IP Cabling Transmission - Passive

POE-1TR is a low cost and easy, speedy solution to allow you to use existing coax cable to send IP camera signal

### Features:

- Use existing coax cable to send IP camera signal
- Passive, no power required
- Terminated with both RJ45 and BNC connections
- Support 10/100Mbps transmission rate
- Transmission up to 984 feet (300 meters) over RG6 cable

### Applications:

- Used in pairs with your RG59/6U cable to exceed the IEEE 802.3 10/100BaseT specification

### Transmission Speed and Distance:

Transmission distance, speed, depend on the quality of the coax cable used. Refer to the following guidelines:

Coax Cable	Link Speed	Distance Max
RG59	Auto 100 Mbps	328 ft (100 M)
RG59	10 Mbps	656 ft (200 M)
RG6U	Auto 100 Mbps	492 ft (150M)
RG6U	10 Mbps	984 ft (300 M)



### Installation View

