

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1110403304](#)
Status: **Active**
Overview: [QSFP+ Interconnect Solution](#)
Description: QSFP+-to-QSFP+ Cable Assembly, 26 AWG, 3.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Packaging Specification PK-111040-051 \(PDF\)](#)

Agency Certification

UL E72548

General

Product Family Cable Assemblies
 Series [111040](#)
 Assembly Configuration Dual Ended Connectors
 Connector to Connector QSFP+-to-QSFP+
 Overview [QSFP+ Interconnect Solution](#)
 Product Name QSFP Plus, QSFP+
 UPC 883906902315

Physical

Cable Length 3.0m
 Circuits (Loaded) MSA
 Gender Plug
 Lock to Mating Part Yes
 Net Weight 353.693/g
 Number of Rows 2
 Packaging Type Bag
 Single Ended No
 Wire Size AWG 26
 Wire/Cable Type Round

Electrical

Impedance 100Ω

Material Info

Reference - Drawing Numbers

Packaging Specification PK-111040-051
 Sales Drawing 1110400001-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)4578-DC (25
 June 2020)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[111040 Series](#)

Mates With

[75586](#) 38 Circuit iPass SMT Connector

Use With

[74750](#) , [74768](#) , [74769](#) EMI Cage

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION