

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0747572301](#)
Status: **Active**
Overview: [QSFP+ Interconnect Solution](#)
Description: QSFP-to-QSFP Cable Assembly, 28 AWG, 3.0m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Test Summary TS-74757-0011-001 \(PDF\)](#)

Agency Certification

UL E72548

General

Product Family Cable Assemblies
 Series [74757](#)
 Assembly Configuration Dual Ended Connectors
 Connector to Connector QSFP-to-QSFP
 Overview [QSFP+ Interconnect Solution](#)
 Product Name QSFP
 UPC 800756775395

Physical

Cable Length 3.0m
 Circuits (Loaded) MSA
 Gender Plug
 Lock to Mating Part Yes
 Net Weight 261.000/g
 Single Ended No
 Wire Size AWG 28
 Wire/Cable Type Round


Electrical

Impedance 100Ω

Material Info

Reference - Drawing Numbers

Sales Drawing SD-74757-0001
 Test Summary TS-74757-0011-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Contained Per -
 D(2020)4578-DC (25
 June 2020)

C,C'-
 azodi(formamide)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[74757](#) Series

Mates With

[75586](#) 38 Circuit iPass SMT Connector

Use With

[74750](#) , [74768](#) , [74769](#) EMI Cage