



SPECIFICATIONS

Model Name	Radeon™ RX 550 4GT LP OC
Graphics Processing Unit	Radeon™ RX 550
Interface	PCI Express x16 (uses x8)
Cores	512 Units
Core Clocks	Boost: up to 1203 MHz
Memory Speed	6000 MHz
Memory	4GB GDDR5
Memory Bus	128-bit
Output	HDMI (Version 2.0) / DL-DVI-D
HDCP Support	2.2
Power consumption	50 W
Recommended PSU	400 W
Card Dimension (mm)	170 x 68 x 38 mm
Weight (Card / Package)	276 g / 508 g
DirectX Version Support	12
OpenGL Version Support	4.5
Maximum Displays	2

CONNECTIONS



1. HDMI
2. DVI-D

FEATURES



DUAL FAN THERMAL DESIGN

Dual fans covers more area of heatsink to take heat away more efficiently.



LOW PROFILE DESIGN

Low Profile design saves space to allow building a slim/small form factor system.



Military Class 4 Components

Using only the highest quality components means you get reliable and stable in-game performance.



OC PERFORMANCE

MSI OC graphics cards are equipped with higher clock speeds out of the box for increased performance.



AMD FreeSync™

Puts an end to choppy gameplay and broken frames with fluid, artifact-free performance at virtually any framerate.



ENHANCED POLARIS ARCHITECTURE

Asynchronous Shaders and an enhanced Geometry Engine power new levels of smooth gameplay performance.



MSI Afterburner

The ultimate overclocking software with advanced control options and real-time hardware monitor.