



24" Smart LED TV with Wi-Fi

- 24" LED TV Freeview DVB-T2 HD channels
- Watch your favourite catch up and streaming entertainment apps
- Built-in Wi-Fi
- HD Ready
- HDMI input for external devices & consoles
- USB 2.0 - Play media files from other devices
- Can be wall mounted (200mm x 100mm bracket not included)

| | EAN | 5060750400517 |
|-------------------------|---------------------------|--|
| General Feature | Model number | C2420RTSF |
| | Screen size | 24" |
| | Max Resolution | 1366 x 768 |
| | HD Ready, Full HD, 4K UHD | HD Ready |
| | Contrast Ratio | 1200: 1 |
| | Brightness | 180cd/m |
| | Display Colours | 16.7M |
| | Viewing Angle | 89/89/89/89(CR≥10) |
| | Cabinet Colour | Black |
| | Wall mounting sizes | 200 x 100mm |
| Reception | TV system | DTV:DVB-T & DVB-C & DVBT2, MPEG 2, MP@ML, MPEG 4 |
| | 5v from antenna | N/A |
| Sound | Stereo system | Yes |
| | Audio output | 2 x 3W |
| Inputs / outputs | RF Antenna | x1 |
| | HDMI | x1 |
| | CVBS | x1 |
| | Audio in | PC x1, CVBS x 1 |
| | Digital Audio Out | x1 |
| | Earphone Out | x1 |
| | USB | x2 |
| | CI | x1 |
| | RJ45 | x1 |

| | | |
|-----------------------|--------------------------------|---|
| Other Features | DVD | Yes |
| | Smart | Yes |
| | Google Assistant | No |
| | Available Apps | Netflix, Prime video, catch up apps |
| | OSD Language | English, Deutsch, Francais, Espanol, Portugese, Italian |
| | Sleep Timer | Yes |
| | EPG (Electronic Program Guide) | 7 Days |

| | | |
|--------------|-----------------------------|--------------------------|
| Power | Power supply | AC 100V-240V - 50Hz/60Hz |
| | Operation Power Consumption | 24W |
| | KWh/annum | 36kWh |
| | Max Power Consumption | 36W |
| | Standby power consumption | <0.5W |
| | Energy Efficiency Class | A |

| | | |
|-------------------|-------------------|---------|
| In the box | Remote Control | Yes |
| | Power Cable | Yes |
| | Warranty | Yes |
| | Battery | AAA x 2 |
| | Quick start guide | Yes |
| | 12 volt cable | No |

| | | |
|-------------------|--------------------------------|-----------------|
| Dimensions | Unit with stand (W x D x H) | 550 x 153 x 354 |
| | Unit without stand (W x D x H) | 550 x 86 x 332 |
| | Weight (kg) | 2.75 |
| | Carton Box Dimension | - |
| | Carton Box Weight | - |