

Lyra

ULTRA-HD MULTIMODE USB MICROPHONE

AKG[®]
by HARMAN



HIGHLIGHTS ■

Ultra-HD Quality Audio

24-bit/192kHz high-resolution converters

Adaptive Capsule Array

Four-capsule mic array provides four user-friendly capture modes

Easy Setup and Universal Compatibility

Intuitive, plug-and-play setup and operation with support for Mac[®] and PC, plus iOS[®] and Android[™] tablets and phones

Headphone Output and Volume Control

Zero latency monitoring while tracking with full control over output volume, mic gain and mute

Versatile Mounting Options

Use with the integrated desktop mic stand or mount to a standard or boom mic stand

Modern Design With Vintage Appeal

Camera-ready styling for on-screen appeal

Complete Production Solution

Includes Ableton Live 10 Lite audio production software

AKG Lyra is an ultra-HD USB microphone built upon AKG's 70-year studio legacy. With pristine sound quality, four optimized capture modes and intuitive on-board controls Lyra is ideal for recording or live-streaming professional-sounding podcasts, YouTube videos, music and more.

Plug-and-play with PC, Mac and your iOS or Android mobile devices via USB. The sophisticated vintage-modern industrial design will keep you inspired at your desk, in the studio and on location. Bundled together with Ableton recording software, AKG Lyra is the ultimate microphone for content creators.

KEY MESSAGES ■

Ultra-HD Audio Quality

The Lyra's advanced circuitry delivers acoustically transparent, 24-bit/192kHz audio resolution, which meets the standards of 4K Ultra-HD projects. An internal self-adjusting shock mount minimizes contact noise, and proprietary Internal Element Overload Prevention automatically reduces noise, eliminates pops and improves signal levels.

Plug-and-Play Universal Compatibility

Easy, plug-and-play setup and usage on PC, Mac, iOS or Android devices via a USB-C connection and tested with the most popular audio and video production software, live streaming and conferencing applications.

Adaptive Capsule Array For Perfect Capture

Lyra's proprietary Adaptive Capsule Array offers four user-friendly capture modes, optimized for any performance or application: Front, Front + Back, Tight Stereo, Wide Stereo.

Modern Design With Vintage Appeal

This distinctive microphone exudes cool at every angle, with sleek industrial stylings accenting a modern, vintage-inspired design. Integrated cable management keeps the workspace streamlined and clutter free.

Lyra

ULTRA-HD MULTIMODE USB MICROPHONE

AKG[®]
by HARMAN

APPLICATIONS ■

- CONTENT CREATION, PODCASTING, VLOGGING & LIVE STREAMING
- INSTRUMENT/VOICE RECORDING
- MOBILE/FIELD RECORDING
- WEB CONFERENCING & VOIP

TECHNICAL SPECIFICATIONS ■

Microphone

Transfer Protocol:	USB 2.0
Transducer:	4 proprietary, permanently polarized back plate, condenser capsules
Capture Modes:	Selectable; Front, Front & Back, Tight Stereo and Wide Stereo
Frequency Response:	20 Hz – 20 kHz
Bit Depth / Sample Rate:	24-bit / 192 kHz
Maximum SPL:	129 dB SPL (0.5% THD)
Power Requirement/Consumption:	5V USB / 75 mA

Headphone Output

Impedance:	16 ohms
Power Output (RMS):	43 mW
THD:	<0.009%
Frequency Response:	20 Hz – 22 kHz
S/N Ratio:	98.0 dB

ORDER SPECIFICATIONS ■

Box Dims (L x W x H):	8.85 x 5.91 x 9.96 in (225 x 150 x 253 mm)
Shipping Weight:	2.83 lb (1.28 kg)
Case Pack Qty:	4
Case Pack Dimensions (L x W x H):	18.46 x 12.56 x 10.98 in (469 x 319 x 279 mm)
Case Pack Weight:	Gross: 12.85 lb (5.83 kg) Net: 8.12 lb (3.68 kg)
AKG SKU:	C44-USB
UPC Code:	885038040804
EAN Code:	9002761048308

IN THE BOX ■

Lyra microphone
2m (6.6ft) USB cable (USB type-C to USB type-A)
Registration card for Ableton Live 10 Lite
Quick start guide, warranty, safety/regulatory sheet



AKG ACOUSTICS GMBH SALZGASSE 2, 5400 HALLEIN, AUSTRIA
AKG ACOUSTICS, U.S. 8500 BALBOA BOULEVARD, NORTHRIDGE, CA 91329, U.S.A.

© 2019 HARMAN International Industries, Incorporated. All rights reserved. AKG is a trademark of AKG Acoustics GmbH, registered in the United States and/or other countries. Features, specifications and appearance are subject to change without notice.

www.akg.com

Issued: 10/2019