



Einhell

CLASSIC

Sliding Mitre Saw

TC-SM 2531/2 U

Item No.: 4300805


Ident No.: 11019

Bar Code: 4006825645637

The Einhell crosscut and mitre saw TC-SM 2531/2 U combines user-friendliness with precision on crosscuts and mitre cuts in workpieces made of wood, laminated panels and plastics. The high-quality turntable comes with an exact angle adjustment facility that can be latched single handedly in various positions. The carbide-tipped precision saw blade achieves outstanding sawing results. The saw comes with a stable underframe which allows a comfortable working height at 84 cm. A pleasant feature is the integrated laser, which simplify and quicken the work enormously. The integrated drag function helps to cut wider workpieces, while the 254mm saw blade enables cutting higher workpieces

Features & Benefits

- Base frame for stable stand and comfortable working height (84cm)
- The included laser makes quick and exact cuts possible
- Turntable with precise angle setting for angular cuts
- Saw head tilts to the left for mitre cutting
- Drag function for wide work pieces up to 310 mm
- Workpiece support on both sides for long workpieces
- All scales are perfectly visible from the working position
- Spindle lock for easy blade change



Technical Data

- Mains supply	230-240 V 50 Hz
- Power	1900 W
- Idle speed	4800 min ⁻¹
- Saw blade	Ø254 x ø30 mm
- Mitre cut	-45° - +0°
- Swiveling range	-45° - +45°
- Cutting width 90° x 90°	230 x 70 mm
- Cutting width 90° x 45°	210 x 70 mm
- Cutting width 45° x 90°	310 x 40 mm
- Cutting width 45° x 45°	210 x 40 mm
- Diameter of suction adapter	36 mm
- max cutting width (90°)	310 mm
- max cutting width (45°)	210 mm

Logistic Data

- Product weight (kg)	17.755
- Gross weight (kg)	20.52
- Dimensions single packaging	740 x 480 x 410 mm
- Pieces per export carton	1 Pieces
- Gross weight export carton	19.9 kg
- Dimensions export carton	750 x 485 x 406 mm
- Container quantity (20"/40"/40"HC)	204 408 466

