

02

0274

# Quicklock circular connectors, IP67



Quicklock flange chassis socket, IP67, size 28, straight version, with metal housing, screw clamps (8-pole version with solder terminals) and protecting cap (IP65)


Approvals:





02/03 poles

1 of 3 08/2020









- 2 and 3 pole versions with screw clamps
- 8 pole version with solder contacts \*b
- port \*c

### **Environmental conditions**

Temperature range -40 °C/+80 °C

### Materials

Insulating body PBT, V-0 according to UL94 Contact bush CuZn, gold-plated Housing Zn alloy, chrome-plated

Cap SI

### Mechanical data

Mating cycles 1700 Insertion force ≤ 130 N Withdrawal force ≤ 120 N

IP67 (protecting cap IP65)1 Protection class

<sup>1</sup> only in locked condition with an appropriate counterpart

## Connectable conductors for screw clamp

Section 2.5-16.0 mm<sup>2</sup>/AWG 14-6 (2-3

poles)

## Connectable conductors for solder area

Section 1.5-4.0 mm<sup>2</sup>/AWG 16-12 (8 poles)

## Electrical data (at Tamb 20 °C)

Contact resistance  $\leq 5 \text{ m}\Omega$ Rated current

50 A (2 poles) 43 A (3 poles) 17 A (8 poles)

500 V AC Rated voltage Rated impulse voltage ≤ 2500 V Creepage distance ≥ 2 mm Clearance ≥ 2 mm Insulation resistance > 500 MΩ

## Associated products

Counterparts ₫ 0254

2 of 3 08/2020



02 0274

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
0274 02	2	4	20
0274 03	3	4	20
0274 08	8	4	20

## Packaging:

in individual plastic bags, in a cardboard box

3 of 3 08/2020