

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0150140413](#)
Status: **Active**
Overview: [Premo-Flex Cable Jumpers](#)
Description: 0.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 101.60mm Cable Length, Gold (Au) Plating, 13 Circuits

Documents:

[Drawing \(PDF\)](#) [Datasheet \(PDF\)](#)
[Product Specification 1501400001-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-------------------------|--|
| Product Family | Cable |
| Series | 15014 |
| Crimp Quality Equipment | Yes |
| Overview | Premo-Flex Cable Jumpers |
| Product Name | Premo-Flex FFC Jumper |
| UPC | 191130093281 |

Physical

| | |
|-------------------------------|-----------------|
| Cable Length | 101.60mm |
| Circuits (Loaded) | 13 |
| Material - Plating Mating | Gold |
| Net Weight | 1.000/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 0.25mm |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | 0.2A |
| Voltage - Maximum | N/A |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|----------------|
| Product Specification | 1501400001-000 |
| Sales Drawing | 150140001-000 |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[15014 Series](#)

Mates With

Easy-On FFC/FPC Connector [5020781362](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION