


SPECIFICATION SHEET

PRODUCT CODE: 778371

Increase your home security and add a little style with this ultra-modern LED Up/Down Garden Bollard light. The cool white light is distributed both up and down, giving the product a great contemporary finish and creating a beautiful lighting effect suitable for any garden, driveway or parking space. The tough aluminium body ensures the bollard light is able to withstand all weather conditions. With an IP54 rating and an 800-lumen light output, the fitting is suitable for outdoor use in any modern or contemporary setting.





SPECIFICATION

Product code	778371
Fitting	Garden Light
Bulb shape	SMD
Wattage	13.2W
Equivalent wattage	105W
Lumens	800lm
Ra	80
Dimmable	No
Beam Angle	120°
Width	160mm
Height	500mm
Depth	75mm
Lifespan	15,000 hours
Warranty	2 Years
Energy consumption	0.0132kW/h
Input frequency	50Hz
Voltage	230-240V
Energy rating	A
Material	Aluminium Body + PC Cover
Packaging	White Box + Colour Label
IP Rating	IP54

OPTICAL TEST PARAMETERS

Voltage	230-240V
Current	0.07A
Power	10W
CCT	No
Ra	80
Lumens	760lm
Lumens per watt	60lm/W
Colour tolerance	<6
Power factor	0.5



TIME LED is part of Pitacs Limited

Bradbourne Point, Bradbourne Drive, Tilbrook, Milton Keynes, Buckinghamshire MK7 8AT
 T: +44 (0)1908 271155 F: +44 (0)1908 640017 E: info@timeled.co.uk W: www.timeled.co.uk



February 2020