



SLIM SURFACE ROUND

V-TAC's LED Lighting range includes lighting that fulfills the needs of various end-users and industries, offering efficient and innovative products that provide modern solutions at an affordable price. We are proud to also provide extended multi-year warranty on our products, as well as detailed support.


One brand, endless solutions..

SKU: 4904 - 1253 940

[View more details](#)

TECHNICAL INFORMATION

Watts:	6
Lumens:	420
Shape:	Round
Input Power:	AC:85-265V, 50/60Hz
Long Life:	20,000 Hours
Unit Color:	White
Body Type:	Aluminium
PF:	>0.9
LED Chip Type:	SMD
CRI:	>80
Operation Temperature:	-25°C to +50°C
Dimmable:	No
Beam Angle:	120°
Color:	3000K
Dimension:	Ø90x24mm



FEATURES

- Strong and sturdy Aluminium body
- High quality power driver ensures reliable lifetime
- Designed with high efficiency LED SMD chips.
- No Lead or Mercury content hence Environment friendly
- Suitable for offices, conference rooms, showrooms, lobbies, cabins, kitchens etc.

CE/EMC

CE/LVD



PACKAGING

Gross Weight (Kgs): 0.17
Unit CBM: 0.00031137
Dimension: Ø90x24mm

MASTER BOX PACKAGING

Box Qty: 50
Qty Per Pallet: 2400
Length (Box) mm: 110
Width (Box) mm: 100
Height (Box) mm: 30

LISTING DETAILS

Commodity Code: 9405403990
EanCode: 3800157605380