

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2093250004](#)  
**Status:** **Active**  
**Overview:** [L1NK Connector System](#)  
**Description:** L1NK 300 Terminal Position Assurance (TPA) Retainer, 3.00mm Pitch, 4 Circuits, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 2093250000-PK-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 2092080000-TS-000 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification 2092080000-PS-000 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification 2092080000-AS-000 (PDF)</a>	

**General**

Product Family	Accessories
Series	<a href="#">209325</a>
Component Type	Terminal Position Assurance
Overview	<a href="#">L1NK Connector System</a>
Product Name	L1NK 300
UPC	193264185832


**Physical**

Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.088/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Application Specification	2092080000-AS-000
Packaging Specification	2093250000-PK-000
Product Specification	2092080000-PS-000
Sales Drawing	2093250000-SD-000
Test Summary	2092080000-TS-000



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)4578-DC (25  
June 2020)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[209325 Series](#)

**Use With**

L1NK 300 Receptacle Housing [2092090004](#)