

Datasheet

IEC Type K, J or T PFA Exposed Welded Tip Thermocouples with Miniature Thermocouple Plug



- Thermocouple types K, J or T to IEC 584
- Fast response, welded exposed junction
- Teflon® PFA insulated twin-twisted lead
- Class 1 cable specification in accordance with BS EN 60584-3:2008
- Tolerance to IEC 584 Class 1
- Miniature plug termination
- Temperature range -75°C to +250°C
- Ideal for test & development applications

Thermocouple type	Conductors	Length	Order Code
Type K	1/0.315mm	1 metre	XF-1534-FAR
Type K	1/0.315mm	2 metre	XF-1225-FAR
Type K	7/0.2mm	1 metre	XF-1535-FAR
Type K	7/0.2mm	2 metre	XF-1226-FAR
Type K	1/0.2mm	1 metre	XF-1536-FAR
Type K	1/0.2mm	2 metre	XF-1227-FAR
Type K	1/0.2mm	10 metre	XF-1228-FAR
Type J	1/0.2mm	1 metre	XF-1537-FAR
Type J	1/0.2mm	2 metre	XF-1229-FAR
Type J	1/0.2mm	10 metre	XF-1538-FAR
Type T	1/0.315mm	1 metre	XF-1230-FAR
Type T	1/0.315mm	2 metre	XF-1231-FAR
Type T	7/0.2mm	1 metre	XF-1232-FAR
Type T	7/0.2mm	2 metre	XF-1233-FAR
Type T	1/0.2mm	1 metre	XF-1539-FAR
Type T	1/0.2mm	2 metre	XF-1234-FAR
Type T	1/0.2mm	10 metre	XF-1540-FAR