


Datasheet

## Leaf Thermocouple Type K IEC With Cable Clamps and Terminating in Standard Plug



- Thermocouple mounted on a stainless-steel shim
- 25x13mm shim
- Junction grounded at tip for fast response
- Rated 350°C
- 2 Metre glassfibre insulated lead with stainless steel overbraid, 7/0.2mm
- Type K Available Fitted with cable clamps and standard thermocouple plug
- Good temperature resistance but not suitable where fluids are present
- Tolerance Class 2 to IEC-584
- Insulation rating -60°C to 350°C (short periods up to 400°C)
- Colour code (cores & jacket) to IEC-584-3

T/C Type	Conductors	Cores	Length	order code
K	7/0.2mm	+Green/-White	2 metres	<b>XF-1547-FAR</b>