

Datasheet

## IEC Type K PFA Exposed Welded Tip Thermocouples with Miniature Thermocouple Plug



- Thermocouple type K to IEC 584
- Fast response, welded exposed junction
- Teflon® PFA insulated twin-twisted lead
- Class 1 cable specification in accordance with BS EN 60584-3:2008
- Tolerance to IEC 584 Class 1
- Miniature plug termination
- Temperature range  $-75^{\circ}\text{C}$  to  $+250^{\circ}\text{C}$
- Ideal for test & development applications

type	Conductors	Length	order code
K	1/0.5mm	1m	<b>XF-1563-FAR</b>
K	1/0.5mm	2m	<b>XF-1564-FAR</b>
K	1/0.5mm	3m	<b>XF-1565-FAR</b>
K	1/0.5mm	5m	<b>XF-1566-FAR</b>
K	1/0.5mm	10m	<b>XF-1567-FAR</b>