



544E

Product no.: 544E

Chain nose pliers with narrow half-round jaws.



Pliers for miniature and standard electronics



Non-reflecting surface, ESD-safe, high grade tool steel



For securely handling components.



[source images](#)

Built to Last - Longest lasting durability on the planet

Weller Erem™ Pliers are designed to ensure an accurate and sure grip every time. Manufactured with uncompromising Swiss quality and created for worldwide applications, including electronics assembly and healthcare, Weller Erem Pliers are built to last. Feel the difference with Weller Erem™ – the proven choice. Every time.

BUILT TO LAST

Longest lasting durability on the planet

+ Precision
Experience precise bending from the high-precision screw joint that enables a smooth action with no jaw overlap

+ Quality
Uncompromising Swiss quality created to be strong and durable

+ 1 Million Movements
Magic Spring™ design enables maximum durability with constant spring force movements

+ Comfort, Security and Grip
Ergonomically-shaped handles provide superior comfort and fatigue-free handling with Maximum Opening Stop Technology

ESD Safe
Made from ESD-safe material to prevent damage to sensitive components



Swiss
Made

weller-tools.com

Weller
Erem





Technical Data

Length mm	120
Jaw length in mm	23
Head width mm	11
Head thickness mm	6
Width of tips in mm	1
Total height of both tips in mm	1.4
Length inches	4.724
Jaw length inches	0.906
Head width Inches	0.433
Head thickness Inches	0.236
Width of tips in Inches	0.039
Total height of both tips in Inches	0.055
ESD-safe	on
Erem applications	Microelectronic
Material	Special tool steel
Weight in g	67
Weight in oz	2.363