



PRODUCT-DETAILS

## TBDL0375-75

### 16MM GALV. STEEL CONDUIT 75M

---

#### General Information

Extended Product Type	TBDL0375-75
Product ID	7TCD012500R0414
EAN	5414363101024
Catalog Description	16MM GALV. STEEL CONDUIT 75M
Long Description	Flexible Metrallic Conduit, Size 3/8 Inch/16mm, Minimum Bend Radius 50mm, Galvanised Steel Core with PVC Jacket, UL and CSA Listed, IP67 Rating, Length 75 Meters

---

#### Ordering

EAN	5414363101024
-----	---------------

---

#### Dimensions

Product Net Depth / Length	75 m
Product Net Weight	78.14 lb 35.438 kg

---

#### Container Information

Package Level 2 Units	1 reel
Package Level 2 Width	32.3 in 820 mm

---

Package Level 2 Height	5.9 in 150 mm
Package Level 2 Depth / Length	32.3 in 820 mm

## Additional Information

Application	Export-Oriented Mechanical and Plant Engineering
Brand / Label	T&B Liquidtight Fittings
Color	Black
Inside Diameter	12.5 mm
Material	Galvanized Steel with PVC Jacket
Nominal Size	16 mm
Number of Batteries	0
Outside Diameter	17.8 mm
Product Name	T&B LIQUIDTIGHT FITTINGS
Product Type	Flexible Conduit - Steel Core
Radius	50 mm
Special Functions	Extremely High Mechanical Stability
Standards	UL E125517, CSA
UPC	786210515847

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TBDL0375-75
Instructions and Manuals	TBDL0375-75

## Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

## Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Liquidtight Fittings

—