



PRODUCT-DETAILS

TBEF0500-60

20MM GALV. STEEL CONDUIT 60M

General Information

Extended Product Type	TBEF0500-60
Product ID	7TCD012500R0445
EAN	5414363076506
Catalog Description	20MM GALV. STEEL CONDUIT 60M
Long Description	Flexible Metrallic Conduit, Size 1/2 Inch/20mm, Minimum Bend Radius 75mm, Galvanised Steel Core with PVC Jacket, Length 60 Meters

Ordering

EAN	5414363076506
-----	---------------

Dimensions

Product Net Depth / Length	60 m
Product Net Weight	51.62 lb 23.41 kg

Container Information

Package Level 2 Units	1 reel
Package Level 2 Width	22.4 in 569 mm

Package Level 2 Height	14 in 356 mm
Package Level 2 Depth / Length	21.3 in 541 mm

Additional Information

Application	Standard Multi-purpose Conduit
Brand / Label	T&B Liquidtight Fittings
Color	Black
Inside Diameter	16 mm
Material	Galvanized Steel with PVC Jacket
Nominal Size	20 mm
Number of Batteries	0
Outside Diameter	21.1 mm
Product Name	T&B LIQUIDTIGHT FITTINGS
Product Type	Flexible Conduit - Steel Core
Radius	75 mm
Special Functions	Flexible, Vde Approved, For Heavy-duty Use
UPC	786210504926

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TBEF0500-60
Instructions and Manuals	TBEF0500-60

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Liquidtight Fittings

—