



PRODUCT-DETAILS

TBEF1000-30G

32MM GALV. STEEL CONDUIT 30M GREY

General Information

Extended Product Type	TBEF1000-30G
Product ID	7TCD012500R0453
EAN	5414363126942
Catalog Description	32MM GALV. STEEL CONDUIT 30M GREY
Long Description	32MM Galvanized Steel Conduit 30M Grey

Ordering

EAN	5414363126942
-----	---------------

Dimensions

Product Net Depth / Length	30 m
Product Net Weight	63.77 lb 28.921 kg

Container Information

Package Level 2 Units	1 reel
Package Level 2 Width	29.5 in 749 mm
Package Level 2 Height	6.3 in

	160 mm
Package Level 2 Depth / Length	29.5 in
	749 mm

Additional Information

Application	Standard Multi-purpose Conduit
Brand / Label	T&B Liquidtight Fittings
Color	Grey
Inside Diameter	26 mm
Material	Galvanized Steel with PVC Jacket
Nominal Size	32 mm
Number of Batteries	0
Outside Diameter	33.1 mm
Product Name	T&B LIQUIDTIGHT FITTINGS
Product Type	Flexible Conduit - Steel Core
Radius	110 mm
Special Functions	Flexible, Vde Approved, For Heavy-duty Use
UPC	786210615400

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TBEF1000-30G
Instructions and Manuals	TBEF1000-30G

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Liquidtight Fittings