



PRODUCT-DETAILS

TBEF2000-15

63MM GALV. STEEL CONDUIT 15M

General Information

Extended Product Type	TBEF2000-15
Product ID	7TCD012500R0459
EAN	5414363076575
Catalog Description	63MM GALV. STEEL CONDUIT 15M
Long Description	63MM Galvanized Steel Conduit 15M

Ordering

EAN	5414363076575
-----	---------------

Dimensions

Product Net Depth / Length	15 m
Product Net Weight	61.79 lb 28.023 kg

Container Information

Package Level 2 Units	1 reel
Package Level 2 Width	27.5 in 699 mm
Package Level 2 Height	10.2 in

	259 mm
Package Level 2 Depth / Length	27.5 in 699 mm

Additional Information

Application	Standard Multi-purpose Conduit
Brand / Label	T&B Liquidtight Fittings
Color	Black
Inside Diameter	51.6 mm
Material	Galvanized Steel with PVC Jacket
Nominal Size	63 mm
Number of Batteries	0
Outside Diameter	60 mm
Product Name	T&B LIQUIDTIGHT FITTINGS
Product Type	Flexible Conduit - Steel Core
Radius	250 mm
Special Functions	Flexible, Vde Approved, For Heavy-duty Use
UPC	786210587615

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TBEF2000-15
Instructions and Manuals	TBEF2000-15

Classifications

ETIM 6	EC001179 - Protective metallic hose
ETIM 7	EC001179 - Protective metallic hose
UNSPSC	39131706
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5535 >> Electrical conduit

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Liquidtight Fittings