

Tab M10 FHD Plus (2nd Gen) [ZA5T0242GB](#)

Product

Lenovo TB-X606F

Region

UKI

Country/Region

United Kingdom

Machine Type

ZA5T

TopSeller

No

Processor

MediaTek Helio P22T (8C, 8x A53 @2.3GHz)

Graphics

Integrated IMG GE8320 GPU

Chipset

MediaTek SoC Platform

Memory

4GB Soldered LPDDR4X-3200

Display

10.3" FHD (1920x1200) TDDI 330nits

Touchscreen

10-point Multi-touch

Expandable Memory

MicroSD card (Up to 256GB)

Storage

64GB eMMC

WLAN + Bluetooth

11a/b/g/n/ac, 1x1 + BT5.0

WWAN

None

Card Slot

MicroSD Card Holder Tray

Bundled Accessories

None

Color

Iron Grey

Case Material

Metal

Camera

Front 5.0MP / Rear 8.0MP

Microphone

2x, Array

VoiceCall

No

Battery

Integrated 5000mAh

Power Adapter

5V / 2.0A

Operating System

Android Pie

Base Warranty

1-year, Depot

EAN / UPC / JAN

194552945978

Announce Date

2019-11-12

Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

[L WWW.LENOVO.COM](#)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

Lenovo Tab M10 FHD Plus (2nd Gen) Platform Specifications

Product Specifications Reference (PSREF)



Processor	MediaTek® Processor MediaTek Helio P22T (8xARM Cortex-A53, up to 2.3GHz)						Camera	Front / Focus Mode		Rear / Focus Mode		Type	Zoom	Flash Light
Graphics	Integrated IMG GE8320 GPU							5.0MP	Fixed Focus	8.0MP	Auto Focus	CMOS	Digital	No
Display	Size	Resolution	Type	Brightness		Color Gamut	Viewing Angle		Audio Dual side speaker, tuned with Dolby Atmos® Dual array microphones (with dedicated DSP), 3.5mm (0.14inch) combo audio / microphone jack (CTIA)					
	10.3" (261.62mm)	FHD (1920 x 1200)	TDDI	Typ. 330nits	Min. 280nits	Typ. 70.3% NTSC	Min. 65% NTSC	160°						
Multi-touch	Capacitive-type multi-touch, supports 10-point touch						Keyboard	None						
Memory	2GB or 4GB / 3200MHz LPDDR4X, soldered to systemboard						Touchpad	None						
Storage	32GB, 64GB or 128GB eMMC (Embedded Multi Media Card), flash memory on board						Security chip	None						
Card slot	One single card slot (WiFi model) or one dual-card slot (LTE model), supports Nano-SIM card + MicroSD card (up to 256GB, FAT32)						Fingerprint reader	None						
Bluetooth®	Bluetooth 5.0						VoiceCall (Opt)	Yes (TB-X606V only)						
WLAN	802.11 a/b/g/n/ac, 1x1, 2.4 GHz / 5 GHz Wi-Fi Dual Bands						Battery type	Li-ion Polymer 5000mAh (Minimum) / 5100mAh (Typical)						
WWAN (Optional)	4G LTE connectivity						Battery life	Standby Time: 1048hrs Online Video playback Time: Up to 8.5hrs Browsing Time: Up to 9hrs <i>* Battery life varies significantly with hardware configurations, settings, usage, & other factors</i>						
LTE Band	GSM:	B2/B3/B5/B8					AC adapter	5V/2A (USB Type-C™) Over 3.5hrs						
	WCDMA:	B1/B2/B5(B6/B19)/B8												
	FDD LTE:	B1/B2/B3(expanded Band3)/B4/B5(B19)/B7/B8/B20												
	TDD LTE:	B38/B40												
NFC	None						Preload	Android® Pie Lenovo applications <ul style="list-style-type: none"> • Tips • Kid's Mode Third-party applications <ul style="list-style-type: none"> • Netflix • Dolby Atmos • Google • Gmail • Google Chrome • Google Photos • Google Play Store 						
WiFi Direct	Yes						<i>*Applications vary from different Android Pie versions</i>							
WiFi Display	Yes						Limited warranty	One of the following, configurable by model: <ul style="list-style-type: none"> • 1-year mail-in service • 2-year/1-yr battery mail-in service • 1-year courier / depot service • 2-year/1-yr battery courier / depot service • 1-year customer carry-in service • 2-year/1-yr battery customer carry-in service • 2-year/1-yr battery courier / depot or customer carry-in service 						
WHDI	None						Environment	Energy Star® 8.0 (TB-X606F, TB-X606X); RoHS-compliant						
FM Radio	Yes						Ports	Two Pogo Pin, one USB Type-C 2.0, supports OTG, 3.5mm (0.14inch) combo audio / microphone jack (CTIA), One single card slot (WiFi model) or one dual-card slot (LTE model), supports Nano-SIM card + MicroSD card (up to 256GB, FAT32) <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>						
A-GPS (Optional)	Yes (LTE model)													
GPS (Optional)	Yes (LTE model)													
Glionass (Opt)	Yes (LTE model)													
Beidou (Optional)	Yes (LTE model)						Buttons	Power key, volume key						
Vibrator	Yes						Note: The specifications above may not be available in all regions							
G-sensor	Accelerometer sensor						Lenovo							
P-sensor	Proximity sensor						March 2020							
L-sensor	Ambient sensor													
E-compass	None													
Hall Sensor	Yes													
Gyroscope	None													
Proofing	None													
Dimensions	WxDxH: 9.61" x 6.03" x 0.32"; 244.2mm x 153.3mm x 8.15mm													
Weight	460g / 1.01lbs													
Case color	Iron Grey or Platinum Grey													
Case material	Metal													

Note: The specifications above may not be available in all regions

Lenovo
March 2020

Tab M10 FHD Plus (2nd Gen)

