

# INSPECTOR™ RC

The NEBO INSPECTOR RC is a powerful 360 lumen **rechargeable, waterproof** (IP67) penlight. The INSPECTOR RC features **FLEX-POWER** and is equipped with a removable steel clip, 4x zoom and 3 light modes (high, low, strobe) and Soft-Touch Technology, which provides momentary operation when the light is off, with the slight touch of the button.

**3 LIGHT MODES (Rechargeable Battery)**

- High (360 lumens) - 1 hour / 125 meters
- Low (120 lumens) - 3 hours / 70 meters
- Strobe (360 lumens) - 25 minutes / 125 meters

**3 LIGHT MODES (AAA Batteries)**

- High (100 lumens) - 1 hour / 90 meters
- Low (30 lumens) - 4 hours / 50 meters
- Strobe (100 lumens) - 25 minutes / 90 meters

**DESIGN**

- Anodized aircraft-grade aluminum
- Impact-resistant and waterproof (IP67)
- 4x adjustable zoom
- Detachable steel belt/pocket clip

**OPERATION**

- Rear-positioned, ON/OFF button
- Soft Touch can be used only when light is OFF

**ACCESSORIES**

- Micro USB to USB charging cable included

**BATTERIES**

- Powered by either 2 AAA batteries or 1 10850 rechargeable battery(included)

**SPECS**

- 0.1375 lbs.
- Length: Compacted: 6.3" / Extended: 6.5"
- Diameter: 0.7"



Actual Size



Display does not include 'Try Me' sample  
**Display Dimensions**  
 (H) 9.41" x (W) 6.5" x (D) 5.875"  
**Gift Box Dimensions**  
 (H) 6.37" x (W) 1.06" x (D) 0.78"

CALIFORNIA REQUIRED WARNING  
 Cancer and Reproductive Harm  
[www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)

UPC CODE	ITEM	DESCRIPTION
645397936220	NEB-POC-0005	INSPECTOR RC
645397936237	NEB-DSP-0011	INSPECTOR RC Display