

## Thunderbolt 3 Mini Dock - Portable Dual Monitor TB3 Docking Station with DisplayPort 4K 60Hz - 1x USB-A (3.2) & GbE - 11" Attached Cable - Laptop Multiport Adapter - Mac/Windows

### **Product ID:** TB3DKM2DPL

This certified Thunderbolt 3 docking station is a compact mini dock, delivering essential connections for productivity. The bus-powered dock connects dual 4K DisplayPort displays, Gigabit Ethernet, and one USB-A (USB 3.2) port and for flexible set up, the attached Thunderbolt 3 cable has an extended length of (11 in./ 28 cm).

Great for editing 4K video or other Ultra HD tasks, this portable Thunderbolt 3 to DisplayPort dock supports 40 Gbps of throughput and 4K resolution at 60Hz on dual HDMI monitors, through a single Thunderbolt 3 port. Run resource-demanding applications on two independent displays without draining system resources.

Connect your laptop to:

- 2x 4K DisplayPort (DP) displays (up to 4096 x 2160p @ 60Hz)

At just 2.4" x 4.9" (6.1 cm x 12.4 cm), this dock takes up minimal room on your desk and in your laptop case. The dock's 28 cm (11 inches) attached cable provides extended reach to reduce port/connector strain on MacBooks and laptops on riser stands, or if needed, offers the flexibility to position dock further away from the laptop on your desk.

- 1x USB 3.2 Gen 1 Type-A port (5 Gbps)
- 1x Gigabit Ethernet port (with PXE Boot and Wake-on-LAN support)

As many high powered, later generation laptops optimally require more than 100W of power to stay charged, some users prefer to use their laptop's power adapter vs. using their docking stations to keep laptops charged.

This bus-powered TB3 mini dock is ideally suited for those users, providing full Thunderbolt 3 docking station performance and functionality, while their workstation laptops are separately charged."

The TB3DKM2DPL is Thunderbolt Certified and backed by a StarTech.com 3-year warranty and free lifetime technical support.

## **Certifications, Reports and Compatibility**

### **Applications**

### **Features**

- **THUNDERBOLT 3 CERTIFIED MINI DOCK:** 40 Gbps video & data throughput, dual monitor 4K 60Hz DisplayPort (DP) output, 1x USB 3.1 Gen 1 Type-A (5Gbps) port & a Gigabit Ethernet port with PXE boot and WoL
- **EXTRA LONG 11 INCH ATTACHED CABLE:** This Thunderbolt 3 docking station's 11in (28cm) attached cable provides extended reach to reduce port/connector strain on MacBooks and laptops on riser stands
- **COMPACT SIZE:** This bus-powered, portable Thunderbolt 3 mini dock is designed for shared and small workspaces; Use this Thunderbolt 3 multiport adapter for work from home or on-the-go/travel use
- **BROAD LAPTOP COMPATIBILITY:** No driver setup; this universal TB3 dock is compatible w/ MacBook Pro 13, 16

and Air, plus Windows-based Thunderbolt 3 laptops like Dell XPS, HP EliteBook, Lenovo X1 Carbon

- FOR HIGH POWERED LAPTOPS: For users who need to use their laptop power adapter as they require 100W or more to keep their laptops charged; but still want Thunderbolt 3 dock performance & functionality
- LATEST MODEL: New version offers same functionality as TB3DKM2DP, plus extra long 11" (28cm) attached cable provides extended reach to reduce port/connector strain on MacBooks and laptops on riser stands

---

#### Hardware

Warranty	3 Years
4K Support	Yes
Fast-Charge Port(s)	No
Displays Supported	2
Audio	No
Interface	Thunderbolt 3
Bus Type	Thunderbolt 3
Industry Standards	1Gb connectivity to any 1000Base-T device (IEEE802.3ab Compliant)  100Mb connectivity to any 100Base-TX device (IEEE802.3u Compliant)  10Mb connectivity to any 10Base-T device (IEEE802.3i Compliant)
Chipset ID	Intel JHL6540 (Alpine Ridge)  Texas Instruments TPS65983A  Parade PS176  ASMedia ASM1042A  Intel WGI210

---

#### Performance

Maximum Digital Resolutions	4K 60Hz
PXE	Yes

---

#### Software

OS Compatibility	Windows 10 (32/64 bit), 8.1 (32/64bit), 7 (32/64bit), Windows Server 2008 R2, 2012(32/64bit), macOS 10.10 -10.15, 11.0
------------------	------------------------------------------------------------------------------------------------------------------------

---

**Power**

Power Source	Bus Powered
--------------	-------------

---

**Environmental**

Operating Temperature	5C to 40C
Storage Temperature	-20C to 70C
Humidity	0% to 95% (non-condensing) at 25C

---

**Physical Characteristics**

Color	Black & Silver
Material	Aluminum and Plastic
Cable Length	11.0 in [28 cm]
Product Length	4.9 in [12.4 cm]
Product Width	2.7 in [69.0 mm]
Product Height	1.1 in [27.0 mm]
Weight of Product	5.2 oz [147.8 g]

---

**Packaging Information**

Package Length	7.7 in [19.5 cm]
Package Width	5.5 in [13.9 cm]
Package Height	1.5 in [37.0 mm]
Shipping (Package) Weight	9.5 oz [270.0 g]

---

**What's in the Box**

Included in Package	Docking Station
	User Manual

---

***\*Product appearance and specifications are subject to change without notice.***

