



Main

Range of product	Harmony Relay
Product or component type	Socket
Contact terminal arrangement	Separate
Product compatibility	Plug-in relay RSB with 2 C/O contact
Shape of pin	Flat
Device short name	RSZ
Sale per indivisible quantity	10

Complementary

[I _{th}] conventional free air thermal current	10 A
[U _e] rated operational voltage	250 V conforming to IEC 300 V conforming to UL
[U _{imp}] rated impulse withstand voltage	4 kV
[U _i] rated insulation voltage	250 V
Fixing mode	Clip-on (35 mm symmetrical DIN rail)
Marking	CE
Length	98 mm
Width	16 mm
Height	60 mm
Net weight	0.042 kg

Environment

Overvoltage category	III
Pollution degree	3
Connections - terminals	Spring clamp terminals (push 'n stay), 1 x 0.5...1 x 1.5 mm ² (AWG 20...AWG 16) flexible with cable end

Spring clamp terminals (push 'n stay), 1 x 0.5...1 x 1.5 mm² (AWG 20...AWG 16) solid without cable end

Standards	IEC 61984
Product certifications	CSA UL EAC
Ambient air temperature for storage	-40...85 °C
Ambient air temperature for operation	-40...85 °C
IP degree of protection	IP20
Dielectric strength	2500 V


Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins


Contractual warranty

Warranty	18 months
----------	-----------

Dimensions



Wiring



Wiring




NOTE: If RSZE08P socket terminals are linked, relay RSB1A160** can be used up to 16A.

Installation



Installation


Push In (Insert Cable)



(1): Insert Wire

Uninstallation

Pull Out (Remove Cable)



(1): Press
(2): Pull Wire