

IPA WIPERS Isopropyl Alcohol Wipes

Product# GPW50

Product Description

IPA WIPERS saturated with isopropyl alcohol is ideal for most general cleaning applications. These alcohol wipes are your daily essential cleaning aid in keeping your work surfaces contaminant-free.

IPA WIPERS is ideal for use throughout your production process in non-critical and non-food production areas, as well as for cleaning surfaces areas around your office spaces and other non-production related areas.

IPA WIPERS contains a mixture of 70% IPA and 30% deionized water. IPA WIPERS is packaged in an environmental-friendly, reclosable slider bag and is easier for waste management.



Features

- Perforated Wipes on a roll
- Low Linting
- Plastic Safe
- Moderate Evaporation for effective breakdown of Contamination
- Reclosable Pouch to keep Wipes moist
- General Purpose Cleaner

Specifications

- 85% Polypropylene 15% Viscose
- Saturated with 70% IPA/30% DI
- Thickness: 0.33mm
- 50 Perforated Wipes on a Roll in reclosable Pouch
- 28cm x 28cm Wipes

Typical Applications

IPA WIPERS is designed for cleaning:

- Work Benches
- Production Areas
- Office Spaces
- Keyboard and Mouse
- Screen and Monitor
- Printers

Typical Product Data and Physical Properties

Boiling Point:	180°F / 82°C Initial
Flash Point (TCC):	68°F / 20°C
Specific Gravity: (Water = 1)	0.88
Vapor Density @ 68°F / 20°C	198 mm Hg
Odor	Mild Alcohol
Solubility in Water	Soluble
Evaporation Rate: (ether =1)	<1
VOC Content*:	
CARB	70%
SCAQMD	616 g/L
Federal	70%
Kauri-Butanol (KB) Number	56
Shelf Life	2 years
RoHS Compliant	Yes

*Volatile Organic Compound (VOC) information is calculated on a weight basis using the VOC definition of California Air Resources Board (CARB) Consumer Product Regulations, South Coast Air Quality Management District (SCAQMD) Rule 102 and the Federal definition published in 40 CFR 51.100(s).

IPA WIPERS

Product # GPW50

Compatibility

IPA WIPERS is compatible with most common plastics and metals. As with any chemical products, surface compatibility should be determined on an inconspicuous area prior to use.

Availability GPW50

Wipes in slider bag, presaturated with 70% IPA and 30% deionized water (50 wipes/tub)

Usage Instructions

For industrial use only. Not intended for medical use.
Do not smoke while using product. Do not use product near sources of ignition, on hot surfaces or energized appliances or equipment.
Read SDS prior to use.

Directions

Open the bag using the slider. Cut or peel open the seal located underneath the slider guides. Pull up the first wipe from center of roll, hold firmly the wipe by pinching the wipe between the two slider guides. Tear away a wipe or multiple wipes as needed while pinching firmly with your other hand. Reclose the bag by sliding the slider back to its initial position. Make sure to slide the slider all the way back to ensure that the bag is fully closed.
When not in use, keep container closed to prevent wipes from drying out.

Environmental Impact Data

HCFC-141b	None
HCFC-225	None
HFC	None
ODP	None

Note:

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. ITW Contamination Control does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.