

New



Code: MFZ160Q

## MINI FRESNEL 160Q ZOOM

40W constant output RGBW LED fresnel with zoom

Designed for short distance wash. The mini Fresnel 160Q zoom is a compact LED Fresnel and powered by 4x40W RGBW LEDs. Featuring 25-90° zoom, even color mixing, DMX and rotary control of dimmer. It deliver a smooth, soft flat field of light. Barn door included for the shape of the light.



### Key features:


- 4x40W COB LEDs (40W R+40W G+40W B+40W W)
- RGBW color mixing
- 25-90° manual zoom
- 16 bit dimming via DMX
- Flat and even color mixing
- Video flicker free
- Super compact, easy for set up
- Rotary, key, DMX control of dimmer
- DMX-RDM compliant, 4 dimmer modes

### Application:

- Micro film shooting
- Small event
- Wedding shooting
- Display lighting




Barn door    Gel frame




### Photometric

R(lx)	273	125	72	43	36	26	23	17	13
G(lx)	620	295	170	108	83	63	58	41	33
B(lx)	151	82	52	33	27	17	15	11	9
W(lx)	740	328	199	132	95	75	69	53	37
Full on(lx)	438	207	120	75	60	43	37	29	25



Distance(m)	2	3	4	5	6	7	8	9	10
Spot Diam(m)	3.18	4.77	6.36	7.95	9.55	11.14	12.73	14.32	15.91

### MAXIMUM SPOT



### Technical Data

Power supply:	AC100-240V, 50/60Hz
Light source:	40W LED
LED color:	40W R+40W G+40W B+40W W
Color temperature:	2700K~8000K
Zoom range:	25-90° manually
Power connection:	PowerCON in
Signal connection:	3-pin XLR in&out(5-pin optional) ARC.1(3CH), AR1.D(4CH), ARC.2(4CH), AR2.D(5CH), AR2.S(6CH), HSV(3CH), STAG(11CH)
Control channels:	
Control mode:	RDM, DMX, Rotary, Master-slave
Housing:	Colour black, Aluminum
Size:	230 x 156 x 279mm(21.6 x 6.1 x 10.9in)
Package(carton):	335 x 218 x 220mm(13.2 x 8.6 x 8.7in)
N.W.:	2.2kg(4.9lb), including barn door
G.W.:	2.8kg(6.2lb)
Accessories:	Power lead, barn door, clamp(optional)
Compliance:	CE, RoHS
Environment:	IP20

THEATRICAL LIGHTING

THEATRICAL LIGHTING