



850
LUMEN



3-15H
RUNTIME



36M
RANGE



IP54/IK07
IP RATING

NEW IL-850R - RECHARGEABLE SLIM INSPECTION LIGHT

- 850 Lumen white COB LED, 6500k
- 150 Lumen white SMD LED top torch, 6500k
- IK07 super tough polycarbonate construction
- Durable non-slip rubber hand grips
- 360° swivel ball joint base with super strong magnet
- Super strong dual rear magnets
- Concealed 180° hanging hook in base
- Smooth dimming roller switch to operate main COB
- Easy press rear moulded switch to operate top torch
- High power 3.7v 2600mAh Li-ion battery
- 5 battery level & charging indicators LED
- Fast 1A USB Type-C charging - 4 hour charge time
- 1m USB charging cable included

BATTERY 3.7v 2600mAh Li-ion Rechargeable Battery

WEIGHT 253g
DIMENSION 40 x 44.5 x 384mm



BATTERY LEVEL INDICATORS



SMOOTH ROLLER SWITCH



USB
TYPE-C

