



USB
TYPE-C



800
LUMEN



2½ - 12H
RUNTIME



38M
RANGE



IP65/IK07
IP RATING

HX800R - COMPACT DUAL LED WORK LIGHT

- 800 lumen 7W white COB LED, 6500K
- Additional 300 lumen 3W SMD LED spot beam, 6500K
- Ultra tough nylon-polymer construction
- 180° rotating stand with super strong magnetic base
- IP65 dust & water resistant
- IK07 shock proof - 2m drop resistant
- Operating temperature -20°C to +50°C
- High power 2600mAh lithium battery
- Battery level and charging indicator lights
- Quick 1A USB Type-C charging - 4 hours charge time
- 1m high quality USB Type-C charging cable (included)

BATTERY 3.7v 2600mAh Li-ion
Rechargeable Battery

WEIGHT 210g

DIMENSION 93.5 x 80 x 35.5mm



BATTERY & CHARGE INDICATORS